

Specifications

		AP50	AP100	AP150	AP200	
ChargePoint® AseptiSafe™	SIP (Steam In Place)	•	•	•	•	
ChargePoint® AseptiSafe™ bio	SIP & H ₂ O ₂ Biodecontamination		•	•		
Size		DN50 (2")	DN100 (4")	DN150 (6")	DN200 (8")	
Containment Performance		Available from <10 ug/m3				
Autoclavable		•	•	•	•	
SIP (Steam In place)*		Up to 2.5 Bar (36 psi)				
Pressure Rating*		Up to 6 Bar (87psi)			Up to 3.5 Bar (50 psi)	
Vacuum Rating*		Full vacuum				
Operation	Manual	•	•	•	•	
	Semi Automatic		•	•	•	
	Fully Automatic		•	•	•	
Product Contact Material	Body	316L	•	•	•	•
		Alloy 22	•	•	•	•
	Seals	FKM	•	•	•	•
		FFKM	•	•	•	•
Passivation (product contact parts)		•	•	•	•	
Connection Interface	Tri-Clamp (BS/ISO/DIN/JIS)	•	•	•	•	
	Aseptic Tri-Clamp / ASME BPE	•	•	•	•	
	Other	Available to suite process / container				

*Pressure/vacuum Rated only when fitted with a suitable pressure/vacuum rated component or accessory